

# SUTPHEN CORPORATION SALES TECHNICAL BULLETIN

## HALE Q-MAX-XS PUMP – BEHIND THE PANEL INTAKE VALVE

### OVERVIEW

Effective immediately, when specifying the Hale Q-MAX-XS pump, we highly **recommend** using a “behind the panel” Master Intake Valve (MIV-electric/manual). This is due to the small frame pump and the close proximity of the 6” intake and the 2.5/3” discharges. We’ve had issues attempting to fit both piston intake valve and NST-to-STORZ adapter on the officer side of the apparatus.



This recommendation applies to all pumper products when utilizing this pump configuration. If you have any other questions or concerns, please contact your designated Sales Applications Engineer (SAE)